

Leona™ 1402S

Asahi Kasei Corporation - Polyamide 66

Tuesday, April 10, 2018

General Information					
Commercial: Active					
 Africa & Middle East Asia Pacific	EuropeNorth America				
Heat Stabilizer					
 Good Flow Good Stiffness	Good ToughnessHeat Stabilized				
Automotive ApplicationsConnectors	Consumer ApplicationsWire & Cable Applications				
	Commercial: Active Africa & Middle East Asia Pacific Heat Stabilizer Good Flow Good Stiffness Automotive Applications	Commercial: Active Africa & Middle East Europe Asia Pacific North America Heat Stabilizer Good Flow Good Stiffness Heat Stabilized Automotive Applications Europe Onth America Heat Stabilized Consumer Applications			

ASTM & ISO Properties 1						
Physical	Dry	Conditioned	Unit	Test Method		
Density / Specific Gravity	1.14		g/cm³	ASTM D792 ISO 1183		
Molding Shrinkage - Flow	1.3 to 2.0		%	Internal Method		
Water Absorption						
Saturation, 23°C		2.5	%			
Equilibrium, 23°C, 50% RH		2.5	%	ISO 62		
Mechanical	Dry	Conditioned	Unit	Test Method		
Tensile Modulus (23°C)	3000	1200	MPa	ISO 527-2		
Tensile Stress						
Yield, 23°C	82.0	52.0	MPa	ISO 527-2		
	79.0	57.0	MPa	ASTM D638		
Tensile Strain						
Yield, 23°C	4.0	24	%	ISO 527-2		
Break	50	250	%	ASTM D638		
Break, 23°C		> 100	%	ISO 527-2		
Flexural Modulus						
	2800	1200	MPa	ASTM D790		
23°C	2700	1100	MPa	ISO 178		
Flexural Strength						
	118	54.0	MPa	ASTM D790		
23°C	113	42.0	MPa	ISO 178		
Taber Abrasion Resistance				ASTM D1044		
1000 Cycles		7.00	mg			
mpact	Dry	Conditioned	Unit	Test Method		
Charpy Notched Impact Strength	6.0	15	kJ/m²	ISO 179		
Charpy Unnotched Impact Strength	No Break	No Break		ISO 179		
Notched Izod Impact	39	150	J/m	ASTM D256		

Disclaimer:

- Data shown are typical values obtained by proper testing methods and shoud not be used for specification purpose. Please use these data for selecting the most appropriate grade suitable for specific usage.
- These data may be changed because of improvement in properties.

 Be sure to read the relevant SDS before handling and use, and always follow the Important Precautions.

 Do not use plastics in any of the following orally-or medically-related applications.
- Orally-related application: any part, device or component which may come into direct oral contact or into direct contact with drinking foods or beverages. For drinking water application, please consult Asahi Ksei Chemicals Corporation.
- Medically-related applications: any part,or component which may be used intracorporeally or which may in dialysis or other processes come into direct or indirect contact with body tissue, body fluids, or transfusion fluids.

Leona™ 1402S

Asahi Kasei Corporation - Polyamide 66

Hardness	Dry	Conditioned	Unit	Test Method
Rockwell Hardness				ASTM D785
M-Scale	80	55		ISO 2039-2
R-Scale	120	108		
Thermal	Dry	Conditioned	Unit	Test Method
Deflection Temperature Under Load				
0.45 MPa, Unannealed	230		°C	ASTM D648
0.45 MPa, Unannealed	190		°C	ISO 75-2/B
1.8 MPa, Unannealed	70.0		°C	ASTM D648 ISO 75-2/A
CLTE - Flow	8.0E-5		cm/cm/°C	ASTM D696
Specific Heat	1670		J/kg/°C	
Thermal Conductivity	0.20		W/m/K	
Electrical	Dry	Conditioned	Unit	Test Method
Surface Resistivity	1.0E+13		ohms	ASTM D257 IEC 60093
Volume Resistivity				
	1.0E+14		ohms·cm	ASTM D257
23°C	1.0E+14		ohms·cm	IEC 60093
Dielectric Strength	20		kV/mm	ASTM D149 IEC 60243-1
Comparative Tracking Index				IEC 60112
3.00 mm	525		V	
Flammability	Dry	Conditioned	Unit	Test Method
Flame Rating (0.75 mm)	V-2			UL 94
Glow Wire Flammability Index				IEC 60695-2-12
3.0 mm	960		°C	
Oxygen Index	26		%	ASTM D2863

Notes

Disclaimer:

For drinking water application, please consult Asahi Ksei Chemicals Corporation.

- Medically-related applications: any part, or component which may be used intracorporeally or which may in dialysis or other processes come into direct or indirect contact with body tissue, body fluids, or transfusion fluids.

¹ Typical properties: these are not to be construed as specifications.

Data shown are typical values obtained by proper testing methods and shoud not be used for specification purpose. Please use these data for selecting the most appropriate grade suitable for specific usage.

These data may be changed because of improvement in properties.

- Be sure to read the relevant SDS before handling and use, and always follow the Important Precautions.

- Do not use plastics in any of the following orally-or medically-related applications.

⁻ Orally-related application: any part, device or component which may come into direct oral contact or into direct contact with drinking foods or beverages.